


FISHER RESEARCH LABORATORY

1212-X

TURN-ON-AND-GO METAL DETECTOR

Easy to use, priced low, & searches deep!



Easy to use, just turn on and go. No extras but lots of performance and the features that really count. Sometimes less is more; compare the 1212-x to any detector in its price range and you'll agree.

FISHER M-SCOPE **CONTROLS**

- **STEREO HEADPHONE JACK:** This jack accepts most stereo and mono head-phones with 1/4" diameter plugs.
- **ON/OFF - TRASH REJECTION CONTROL:** All metals are detected when turned to zero. Most small pieces of metal trash are rejected at the maximum level of ten. Most ground minerals are ignored at all settings.

FISHER M-SCOPE **FEATURES**

- **Automatic** ground rejection and tuning
- **Silent**, no threshold operation
- **VLF** Slow-motion discrimination
- **Full range** discrimination control
- **1/4" Stereo/mono** headphone jack
- **Patented double derivative electronics** (U.S. Patent 4,514,692)
- **Only 2.9 pounds**
- **Flexon grip**
- **Only one 9 volt transistor battery**
- **Simple one-knob operation**
- **Low price**

• **LIFETIME LIMITED WARRANTY**

for a Lifetime of Service & Satisfaction!

FISHER M-SCOPE

\$ince 1931



FISHER RESEARCH LABORATORY

1212-X

Subject to improvement, modification or change without notice.

SPECIFICATIONS

SEARCH MODE

VLF-Discrimination, Slow Motion ⁴

FREQUENCY

VLF-Search.....4.2 KHz
Audio Target Response.....450 Hz ³

LENGTH

Extended.....54.5" ²
Collapsed.....40.5" ²

WEIGHT

2.9 lbs ²

CONTROL FUNCTIONS

Single Knob, Off/On
Trash Rejection

SPECIAL FEATURES

Stereo/Mono Headphone Jack (1/4")
Built-in Speaker

SEARCH COIL

Type.....Concentric/ Coplanar
Diameter.....8"
Shielded.....100% E.S.I. ⁵
Interchangeable.....No

BATTERY

Single 9V Transistor

BATTERY LIFE

Carbon Zinc.....10-15 hours ^{2 6}
Alkaline.....25-35 hours ^{2 6}

WARRANTY

Lifetime Limited Warranty*

*warranty may vary outside of the United States, warranty applies to the original purchaser only. see your dealer for details

NOTES

1. Subject to improvement or modification without notice.
2. Approximate.
3. Pulsegate Unipolar Audio Processing. Advanced Fisher circuitry which allows silent operation below "audio threshold tone" with no loss in sensitivity.
4. The 1212-X is a motion metal detector. The coil must be moving at least slightly to detect a target.
5. Electro-Static-Insulated to eliminate certain types of false signals.
6. Use of headphones may increase battery life up to 100%.

ACCESSORIES

Standard Equipment:
Operation Manual

Optional Equipment:
Coil Covers
Hard Carrying Case
Carry Bag
Fisher Phones
Stereo Phones

ORDERING INFORMATION Call 1-800-M-Scope-1 • 1-800-672-6731 • for a Dealer Near You

For More Information Contact:

FISHER RESEARCH LABORATORY
200 W. Willmott Rd., Los Banos, CA 93635-5501
T 209.826.3292 F 209.826.0416
www.fisherlab.com email: info@fisherlab.com

Inquiries outside of the U.S. Mexico & Canada Contact:

FISHER EXPORT DEPARTMENT
280 State Street, Suite 202, North Haven, CT 06473 USA,
T 203.230.4130 F 203.248.8093
email: fisher@exportdept.com